





X8011-III

Offline X-ray system for manual and automated inspection


Best Inspection Results Thanks to Maximum System Flexibility




Partial view of a QFN



Detail of a medical product



Chip component with orthogonal radiation



BGA with partially defective solder joints

Outstanding resolution and magnification, brilliant and detailed X-ray images

First-class system components: powerful X-ray tubes and high-quality flat-panel detectors

Highest system flexibility and perfect test piece handling

Viscom software XMC, SI, and vVision: easy system operation, rapid inspection plan compilation, extensive analysis tools

3D reconstructions with XVR computed tomography (CT) from Viscom

Viscom Quality Uplink for optimizing costs, while ensuring process reliability and enhancement of product quality on a lasting basis


Worldwide service and application support at the customer, by phone and remote maintenance

Adequate visual inspection of connections belonging to SMD components such as BGA, QFN or QFP is impossible. They remain largely hidden. The same applies to surface soldering in power electronics. Above all, these must also be flawless inside to ensure reliable heat dissipation. Special inspections – for example to rule out assembly errors in a prototype or to document a complaint – should be non-destructive in the same way. In many such cases, optimum quality assurance and defect analysis can only be achieved via X-ray. Here, a modern offline system offers a wide range of possibilities. As with other inspection technologies, Viscom has state-of-theart solutions ready for the most demanding requirements.



The inspection results of the X8011-III system can be linked and evaluated with images and data from SPI, AOI and AXI for precise defect analysis and process optimization using Viscom Quality Uplink.

At the verification station of the X8011-III, a lot of information from the line is available in addition to the **sharp** and detailed MXI images. Causes of defects are therefore traced quickly and reliably. Fully automatic X-ray analyses can be carried out on the X8011-III just as effectively as is familiar from inline assembly inspection in large-scale SMD production. This makes the system ideal for offline quality inspection of medium quantities and small batches, among other applications. Under vAI, Viscom offers solutions with artificial intelligence – e.g. for reliable segmentation of voids in solder joints.




XVR CT analysis: volume image of a turbine

For very special components and other demanding special inspections, XMC software from Viscom provides the appropriate tools on the system. The application range of the X8011-III thus extends from random test piece analysis and inspection of individual devices, assemblies and components to automated start-up support for new product series and efficient quality control in high-mix, low-volume production.

Extensive analysis functions and intuitive operation enable simple and precise inspection. If individual sectional images or layers from 3D reconstructions are required for even better localization of defects, Viscom's unique XVR computed tomography comes into play on the system. The optional XMC Inspection Report add-on in turn automatically generates documents with inspection images and important information such as the settings of the X-ray tube and detector, manufacturing defects detected on the inspection object, or the level of radiation dose in order to comply with limit values even for sensitive components.

An open microfocus transmission tube (up to 200 kV) from Viscom ensures really high resolution in the system. Closed direct beam tubes (up to 180 kV) are also available. In continuous operation, both tube types impress with their very stable X-ray radiation. Thanks to state-of-the-art digital flat-panel detectors, perfect image quality is achieved even at the highest magnifications.

Technical Specifications



		X8011-III eco	X8011-III plus	X8011-III flex
X-ray technology	X-ray tube	Sealed microfocus X-ray tube or open microfocus transmission tube (optionally also TXD X-ray tube, $<$ 1.5 μm)		
	High voltage	20 - 130 kV / 20 - 180 kV (sealed); 20 - 160 kV / 20 - 200 kV (open)		
	Tube current	50 - 300 μA / 5 - 1000 μA		
	Target power	Max. 20 W / max. 40 W Max		Max. 40 W
	Geometric magnification	Max. 35 times / max. 2650 times		Max. 2650 times
	Image converter	High resolution 7.3" FPD, 14 bit High resolution 11" FPE 14 bit (optional 16 bit)		High resolution 11" FPD, 14 bit (optional 16 bit)
	Verified resolution (at 90 kV/80 μ A)	< 16 - 50 μm / < 4 μm / < 1.5 μm*		
	Detector swivel range, additionally via rotation and tilt axis +/- 45° (90°)	0°	0° - 60°	
	X-ray cabinet	Designed to meet requirements for fully protected devices in accordance with German Radiation Protection Act (StrlSchG), German Radiation Protection Ordinance (StrlSchV), CE mark and additional international standards for worldwide use. Radiation leakage rate $<1~\mu Sv/h$		
Software / system computer	User interface	Viscom XMC / Viscom SI optional / vVision-ready		
	Available software packages	Analysis software (BGA, QFN, THT, ACA); fully automatic Viscom SI analysis software; automatic inspection report; XVR CT software (planar, rotational); layer image analysis; Viscom HARAN and vVerify verification station; Viscom Quality Uplink to SPI, AOI and AXI from Viscom; Windows® (system computer operating system)		
	Monitor	High-resolution 27" LCD display for special depiction of grayscale values in the SMT and electronics sectors (DICOM Standard)		
Inspection object handling	Manipulator	X-Y-Z	X-Y-Z plus rotating platform	
	Max. travel range of table	Horizontal x/y axis: 460 mm x 435 mm (18.1" x 17.1"); vertical z axis: 290 mm (11.4")		
	Max. travel range of rotation module	-	Horizontal x/y axis: 350 mm x 430 mm (13.8" x 16.9") Vertical z axis: 290 mm (11.4"), n x 360°	
	Inspection object weight	Up to 10 kg / 22 lbs (5 kg / 11 lbs with rotation module)		
	Test piece change	Motorized window opening		
	Optional additional axes available	Yes		
Other system data	Power requirements	208 V, 60 Hz, 3P/PE +/- 10%; average power consumption 0.9 kWh		
	System dimensions	1255 mm x 2047 mm x 1865 mm (49.4" x 80.6" x 73.4") (W x H x D)		
	Weight	2500 kg (5512 lbs)*		

*Depending on the configuration

Our international subsidiaries and representatives can be found at:

#Viscom_X8011-III_EN_LET23060003 | © Viscom AG. All rights reserved. | Specifications subject to change without notice. Windows® is a registered trademark.